



	Bestell-Nummer /PART NO versilbert /silverplated	ϕ	Leiterquerschnitt wire gauge		Abisolierlänge der Litze stripping length
			mm ²	AWG	
Stiftkontakt male contact	09 35 000 6103	1,15	0,5	20	6,0
	09 35 000 6104	1,3	0,75	18	
	09 35 000 6105	1,45	1,0	18	
	09 35 000 6106	1,75	1,5	16	
	09 35 000 6107	2,25	2,5	14	
Buchsenkontakt female contact	09 35 000 6203	1,15	0,5	20	6,0
	09 35 000 6204	1,3	0,75	18	
	09 35 000 6205	1,45	1,0	18	
	09 35 000 6206	1,75	1,5	16	
	09 35 000 6207	2,25	2,5	14	

All Dimensions in mm
Original Size DIN A 4

Techn. Character.			
	Dat.	Name	Massstab/ Scale 2:1
Detail.	28.03.07	Bor	
Insp.		FER	
Stand.			

Nicht tolerierte Masse! Free size tolerances

Han P Kontakte gedreht 16A
Han P contacts twisted 16A

412827		
Mod.	Dat.	Name

HARTING Electric GmbH & Co. KG
D-32339 Espelkamp

TB 09 35 000 6...
Sub.

Blatt/ page
/